



Main

Range of product	Canalis
Product or component type	End cover
Product compatibility	KBB
[I _e] rated operational current	40 A
Offer type	Spare part
Colour	White (RAL 9003)

Complementary

Mounting location	Side of trunking
Mounting mode	By clips
Mounting support	Busbar
Width	46 mm
Depth	30 mm
Height	46 mm

Environment

IP degree of protection	IP55 conforming to IEC 60529
Standards	IEC 61439-6 IEC 60439-2

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes

Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------

