

UN 38.3 Lithium Battery Test Summary – TS#15

Battery or Product Model Number

Model Number:	IMR18650-1200mAh
Description:	3.7V 1200mAh 4.44Wh rechargeable lithium-ion battery

Battery or Product Manufacturer's contact Information

Name:	Xinxiang Hongli Supply Source Technology Co Ltd			
Address:	West section of Xinglong Road, XinXiang Economic Development Zone, XinXiang County, XinXiang			
City:	Henan	Country:	Peoples Republic of China	
Telephone:	+86 373 5632 158	E-mail:	774753828@qq.com	Website: www.xxshldy.com

Test Laboratory Information


Name:	Shanghai Institute of Chemical Testing Co Ltd			
Address:	200062 No.345 East Yunling Road, Putou			
City:	Shanghai	Country:	Peoples Republic of China	
Telephone:	+86 21 3176 5555	E-mail:	battery@ghs.cn	Website: www.ghs.cn

Battery Description

Cell or Battery:	IMR18650-1200mAh	Physical Description of the cell / battery:
Cell or Battery Type (lithium ion or lithium metal):	Lithium-ion	Cylindrical lithium-ion rechargeable cell
Watt-hour rating (Wh):	4.44Wh	
Battery Weight (g):	34.8g	

Test Report ID Number:		1124110718		Date of test report:	01/01/2015
List of Tests Completed:					
Yes	No		Pass	Fail	Additional Comments:
X		Test T.1: Altitude simulation	X		
X		Test T.2: Thermal test	X		
X		Test T.3: Vibration	X		
X		Test T.4: Shock	X		
X		Test T.5: External Short Circuit	X		
X		Test T.6: Impact/Crush	X		
	X	Test T.7: Overcharge			
X		Test T.8: Forced Discharge	X		

Signature with name and title of signatory as an indication of the validity of information provided:



Name: Tim Walker

Position: Product Compliance Manager Europe