



NEW LED Dimmer from MK Electric offers the widest lamp compatibility for a reliable dimming solution and allows the user to create ambience for comfortable surroundings.

Product Specifications

- MK Electric is the first leading manufacturer to offer a LED dimming solution across its wiring devices range
- Available as a single or double dimmer, in MK Logic Plus and MK Grid Plus*
- MK Logic Plus product is rated 4 – 70W (300W/240VA)
- MK Grid Plus product is rated 4 – 70W (220W/180VA)
- Compatible with tungsten filament, low voltage halogen and **dimnable LED lamps**
- Greater user control, with a minimum load adjustment control on dimmer switch
- Maximum 10 lamps per circuit
- Intelligent load protection will prevent lamp wattage exceeding rating of dimmer



Reduce energy costs

LED lighting technology delivers enhanced lamp endurance and energy savings. Dimmable LED lamps can increase energy savings, allowing you to reduce energy costs further.

Achieve a consistent look

The MK LED Dimmer is available in a wide range of decorative finishes to compliment interior design styles. Matching wiring devices including sockets and switches are available to ensure a consistent look and feel.

A perfect match

The MK LED Dimmer has been tested with leading lamp manufacturers and is compatible with tungsten filament, low voltage halogen and a wide range of dimmable LED lamps.

Decorative LED Dimmer Finish Selector



*Grid Plus range is available in 14 colour options, with black or white inserts. The Module is designed to be used with MK Electric's decorative range of Aspect, Edge, Albany Plus cover plates.

Part Number	Description
Logic Plus Range	
K1523WHILV	1 Gang 2 Way 40-300W/240VA/4-70W LED Single Intelligent Dimmer
K1524WHILV	1 Gang 2 Way 40-300W/240VA/4-70W LED Double Intelligent Dimmer
Decorative Edge, Aspect and Albany Plus Range	
K4511WHILV	1 Module 2 Way 40-220W/180VA/4-70W LED Dimmer inc. - Plastic cap - White Trim
K4511BLKLV	1 Module 2 Way 40-220W/180VA/4-70W LED Dimmer inc. - Plastic cap - Black Trim
K4511BSSBLV	1 Module 2 Way 40-220W/180VA/4-70W LED Dimmer inc. - Metal cap - Brushed Stainless Steel, Black Trim
K4511BSSWLV	1 Module 2 Way 40-220W/180VA/4-70W LED Dimmer inc. - Metal cap - Brushed Stainless Steel, White Trim
K4511LBSWLV	1 Module 2 Way 40-220W/180VA/4-70W LED Dimmer inc. - Metal cap - Lacquered Brushed Steel, White Trim
K4511LBSBLV	1 Module 2 Way 40-220W/180VA/4-70W LED Dimmer inc. - Metal cap - Lacquered Brushed Steel, Black Trim
K4511SAAWLV	1 Module 2 Way 40-220W/180VA/4-70W LED Dimmer inc. - Metal cap - Silver Anodised Aluminium, White Trim
K4511SAABLV	1 Module 2 Way 40-220W/180VA/4-70W LED Dimmer inc. - Metal cap - Silver Anodised Aluminium, Black Trim
K4511BRCWLV	1 Module 2 Way 40-220W/180VA/4-70W LED Dimmer inc. - Metal cap - Brushed Chrome - White Trim
K4511BRCBLV	1 Module 2 Way 40-220W/180VA/4-70W LED Dimmer inc. - Metal cap - Brushed Chrome - Black Trim
K4511POCWLV	1 Module 2 Way 40-220W/180VA/4-70W LED Dimmer inc. - Metal cap - Polished Chrome - White Trim
K4511POCBLV	1 Module 2 Way 40-220W/180VA/4-70W LED Dimmer inc. - Metal cap - Polished Chrome - Black Trim
K4511SAGWLV	1 Module 2 Way 40-220W/180VA/4-70W LED Dimmer inc. - Metal cap - Satin Gold - White Trim
K4511SAGBLV	1 Module 2 Way 40-220W/180VA/4-70W LED Dimmer inc. - Metal cap - Satin Gold - Black Trim
K4511WHIWL	1 Module 2 Way 40-220W/180VA/4-70W LED Dimmer inc. - Metal cap - Porcelain White - White Trim
K4511LIVWLV	1 Module 2 Way 40-220W/180VA/4-70W LED Dimmer inc. - Metal cap - Lustrous Ivory, White Trim
K4511LBKBLV	1 Module 2 Way 40-220W/180VA/4-70W LED Dimmer inc. - Metal cap - Lustrous Black, Black Trim
K4511PBRWLV	1 Module 2 Way 40-220W/180VA/4-70W LED Dimmer inc. - Metal cap - Polished Brass, White Trim
K4511PBRBLV	1 Module 2 Way 40-220W/180VA/4-70W LED Dimmer inc. - Metal cap - Polished Brass, Black Trim
K4511TIRBLV	1 Module 2 Way 40-220W/180VA/4-70W LED Dimmer inc. - Metal cap - Textured Iron, Black Trim
K4511DBZBLV	1 Module 2 Way 40-220W/180VA/4-70W LED Dimmer inc. - Metal cap - Textured Desert Bronze, Black Trim
K4511ABSBLV	1 Module 2 Way 40-220W/180VA/4-70W LED Dimmer inc. - Metal cap - Antique Brass, Black Trim
K4511TCOBLV	1 Module 2 Way 40-220W/180VA/4-70W LED Dimmer inc. - Metal cap - Textured Copper, Black Trim

MK Electric

UK

The Arnold Centre, Paycocke Road, Basildon,
Essex, SS14 3EA, United Kingdom
Customer Service Tel 01268 563404
Customer Service Fax 01268 563405
E-mail mkorderenquiries@honeywell.com

Technical

Tech Helpline Tel 01268 563720
Tech E-mail mk.technical@honeywell.com

www.mkelectric.co.uk

Reference UKMK359-0213-EN
February 2013
© 2013 Honeywell International Inc.

