



Housing units FLCTE40-XL (Series FLCTE)

two-bolt flanged housing units, cast iron, eccentric locking collar, P seals, without relubrication facility

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

d	40 mm
H	150 mm
U	46,3 mm
A ₁	24 mm
A ₂	13,5 mm
B ₁	43,8 mm
d _{3 max}	58 mm
J	119 mm
L	100 mm
N	14 mm
m	1,32 kg Mass

C_r	34500 N	Basic dynamic load rating, radial
C_{0r}	19800 N	Basic static load rating, radial
	LCTE08	Designation of housing
	RAE40-XL-NPP-B	Designation of bearing



