

## Connection Units

Chrome and Satin Chrome



### Description

This uniquely shaped range is easy to install, with coloured terminals, clear white terminal markings and is supplied in individual display boxes.

### Features

- black or white inserts available
- matching metal rocker versions
- lockable fuse carrier for safety isolation
- captive fuse barrier
- clear white terminal markings
- colour coded terminals
- discreet neon versions
- neon leads enclosed
- 2 earth terminals
- captive and backed out terminals
- terminals have large lead-ins
- 25 year guarantee

### Range

#### *plastic switch rockers*

unswitched	1910
unswitched with flex outlet	1911
switched DP	1913
switched DP with neon	1914
switched DP with flex outlet	1915
switched DP with neon and flex outlet	1916

#### *metal capped switch rockers*

switched DP	2913
switched DP with neon	2914
switched DP with flex outlet	2915
switched DP with neon, flex outlet	2916

#### *Prefix with finish*

chrome	CH
satin chrome	SC
white or black inserts	W or B

### Technical Specification

voltage rating	250Vac
current Rating	13A
contact gap	3mm

no user serviceable parts, except BS 1362 fuse links

### Back Boxes

minimum recommended depth

	Flush 25mm	Dry lining 35mm
1g	DB162	DB2540

### Standards

- BS 1363 Part 4 as applicable

### Terminal Capacity

	2.5mm <sup>2</sup>	4mm <sup>2</sup>	6mm <sup>2</sup>	10mm <sup>2</sup>
L & N	4	3	2	1

## DETA

Kingsway House, Laporte Way  
Luton, Beds LU4 8RJ

Tel. +44 1582 544 500 Fax: +44 1582 544 501  
Technical Helpline +44 1582 544 548