

3028 30

Hydraulic press with moving piston

CE

Features:

- Maximum capacity: 30 t
- Manual vertical top adjustment
- Sliding piston
- Hydraulic safety in case of overloading
- Gauge
- Set of V-shaped prisms

	art.	A mm	B mm	C mm	D mm	E mm	F mm	G mm	H mm	
 030280030	3028 30	850	540	1850	1650	990	240	540	148	132

