Features

- 132mm cubic-design multi-tone alarm sounder
- Max. 113 dB (A) sound pressure
- Sound pressure infinitely adjustable by potentiometer
- 32 tones can be selected, 3 tones can be switched externally
- Tone frequency, 150Hz – 2.9kHz
- Optional mounting type using metal bracket
- High degree of protection IP 66
- 24-48V AC/DC supply voltage

RS PRO Sounder

Auer Signal 0697168

RS Stock No..: 0697168

RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- A comprehensive multi-tone sounder with a square 132mm design
- Offers a high degree of protection (IP66) and, with IK09, is particularly impact-resistant and therefore vandal-proof.
- Up to 32 tonnes can be selected providing up to 113db of sound pressure with up to 3 tones that can be switched externally.
- Sound pressure can be infinitely adjustable by potentiometer with a tone frequency between 150Hz to 2.9kHz
- Polycarbonate housing (red) that can be mounted either vertically or horizontally with the optional mounting metal bracket.
- For industrial and general applications.
- Full mounting accessory package available

General Specifications

Housing	Polycarbonate red (RAL 3000)
Type of Mounting	Any. Sound outlet opening at bottom or horizontal
Fitting	4 bolts / screws
Cable Entry	Back: Grommet 5-10mm. Side: Cable Gland M20
Connection	Screw/plug-in terminal up to 2.5mm²
Tone	32 Tones. 3 Tones can be switched externally
Duty Cycle	100%
Impact Resistance	IK09

Mechanical Specifications

Dimensions	132mm (w) x 133mm (d) x 132mm (h)
Mounting Style	Screw Mount
Weight	600g

Electrical Specifications

Supply Voltage	24 - 48 V AC/DC, 50-60Hz
Volume	113 dB
Tone Frequency	150 - 2.9kHz
Current Type	AC/DC
Current Consumption	230mA

Protection Category

IP Rating	IP66

Operation Environmental Specifications

Maximum Temperature	+60°C
Minimum Temperature	-30°C

Approvals

Compliance/Certifications	CE
Declarations	RoHS Compliant / REACH