



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-293722-2

NECTOR M PIN HSG FREE HANGING
7P CODE B

Customers Also Bought



TE Part #1879838-1

3W SM M/OX 5% 680R REELED




TE Part #1-293607-1

NECTOR M CABLE NUT DIA 7.5-8.4
MM



TE Part #2328461-1

280 POS., CONNECTOR ASSEMBLY,
SLIVER 2.0



TE Part #7-1879627-1

H4P 8K2 1% 100PPM



TE Part #1-293468-1

NECTOR M SKT HSG FREE HANGING
CODE A



TE Part #293722-1

NECTOR M PIN HSG FREE HANGING
7P CODE A



TE Part #7-2176392-6

RQ 1206 806K 0.1% 10PPM 5K RL



TE Part #2170785-5

CAGE ASSY, 1X4, QSFP28, GASKET,
HS, LP



TE Part #CAT-H857-H342125

AMP HPI 1.25 mm Headers

Documents

Product Drawings

NECTOR M PIN HSG FREE HANGING 7P CODE B

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_293722-2_A_c-293722-2-a.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_293722-2_A_c-293722-2-a.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_293722-2_A_c-293722-2-a.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Agency Approvals

[Agency Approval Document](#)

English