

Product Technical Sheet

07 Apr 2021 09:39



530.01610

SURFACE MOUNTING SOCKET

16A 2P 20-25V 50Hz 60Hz Screw terminals

Product Approvals



TECHDATA		STANDARDS AND LAWS	
Type of product	SURFACE MOUNTING SOCKET	EN 60309-1 (1999)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
Commercial series	IEC309 Series	EN 60309-2 (1999)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 2: Dimensional interchangeability requirements for pin and contact-tube accessories of harmonized configurations
Synthetical description	SURFACE MOUNTING SOCKET		
Mounting version	SURFACE MOUNTING		
Rated current	16A		
Poles	2P		
Rated voltage (range)	0-50V		
Rated voltage	20-25V		
Working frequency	60Hz		
Working frequency	50Hz		
Colour	VIOLET		
Material	THERMOPLASTIC		
Protection degree	Splash proof		
Protection degree IP	IP44		
Types of available outlets	ANGLED		
Terminals	Screw terminals		
Cable outlet	M25X1,5		