

MGM 11-1220X610X100-01



Application:EPA-filter for standard applications

Type:EPA-filter

Frame:Electro Zink sheet

Gasket:Polyurethane

Media:Glass fibre

Separators:Hot melt beads

Sealant:Polyurethane

Efficiency according to EN 1822:E11

MPPS efficiency:≥95% MPPS

Temperature/Humidity:70°C/100% RH maximum in continuous service

Remarks:All filters are scan tested

Note:Frame available in MDF-board.

Article number	Type	Size	Area (m2)	Air flow (m3/h)	Pressure drop (Pa)
CC6000EPA	CLOSEPLEAT /CamCleaner 6000	MGM 11-1220X610X100-01	24,56	1206	42

