

Produktdatenblatt

0-179 N W/230

EAN-No. 4000896219292



880 • • 3/8
10 • 11 • 12 • 13 • 14 • 15 •
16 • 17 • 18 • 19 • 21 • 22



8816HP • 10 3/8



8820 • 10 3/8 • 10 3/8



8821 • 10 3/8 • 10 3/8
8821-3 • 8821-6 • 8821-10



8858-2 • 6.3 1/4 • 10 3/8



900 • • 12 1/2
10 • 11 • 12 • 13 • 14 • 15 •
16 • 17 • 18 • 19 • 20 • 21 •
22 • 23 • 24 • 26 • 27 • 28 •
30 • 32



900E • • 12 1/2
E10 • E12 • E14 • E16 •
E18 • E20



915 • 12 1/2



916HP • 12 1/2



917-5 • 12 1/2 • 12 1/2



918-10 • 12 1/2 • 12 1/2



920 • 12 1/2 • 12 1/2



958-2 • 10 3/8 • 12 1/2



1058-2 • 12 1/2 • 20 3/4



2204N • • 1/4
2 • 2.5 • 3 • 4 • 5 • 6



2208N • • 1/4
0.5 x 4 • 0.6 x 4.5 •
0.8 x 5.5 • 1 x 6



2215N • • 1/4
PH1 • PH2 • PH3



2216N • • 1/4
PZ1 • PZ2 • PZ3



2223N • • 1/4
T6 • T7 • T8 • T9 • T10 •
T15 • T20 • T25 • T27 •
T30 • T40



2223N • • 1/4
T10H • T15H • T20H •
T25H • T27H • T30H



2239N-6 • 6.3 1/4 • 6.3 1/4



2250-1 • 6.3 1/4 • 6.3 1/4



163-516/10N
 •



811 •
0.5 x 3 • 0.8 x 4 • 1 x 5.5 •
1.2 x 6.5



811PH •
PH1 • PH2



811K •
0.6 x 3.5 • 1 x 5.5



811KPH •
PH1 • PH2



163-525/40
 •



450N •
6 x 7 • 8 x 9 • 10 x 11 •
12 x 13 • 14 x 15 • 16 x 17 •
18 x 19 • 21 x 22 • 24 x 27 •
30 x 32 • 34 x 36



600N •
6 • 7 • 8 • 9 • 10 • 11 • 12 •
13 • 14 • 15 • 16 • 17 • 18 •
19 • 21 • 22 • 24 • 27 • 32



630 •
6 x 7 • 8 x 9 • 10 x 11 •
12 x 13 • 14 x 15 • 16 x 17 •
18 x 19 • 20 x 22 • 21 x 23 •
24 x 27



163-526/41N
 • • •



811 •
0.4 x 2.5 • 0.5 x 3 • 0.8 x 4 •
1 x 5.5 • 1.2 x 6.5



811PH •
PH0 • PH1 • PH2



811T •
T10 • T15 • T20 • T25 •
T27 • T30



811K •
0.6 x 3.5 • 1 x 5.5



811KPH •
PH1 • PH2



811S •
0.8 x 4.5 • 1 x 5.5 • 1.2 x 7



811SPH •
PH1 • PH2 • PH3



2105LG/9H •



2116LG/8H •