

Specifications for TLS 2200/TLS PC Link Labels

Adhesive	Permanent Acrylic
Application	Voice & Data Communication; Wire & Cable Marking
Approval/Compliance	UL Recognised
Article No.	018527
Brady Material No.	B-427
Material Type	Self-laminating Vinyl
Colour	Yellow/Transparent
Finish	Matt
Description	Labels for the TLS2200® & TLS PC Link™ Thermal Transfer Portable Printers. Please Note: This material is UL approved with its respective ribbon. See the Recommended Ribbon Series for the appropriate ribbon to use. TLS2200® parts can also be printed on the BMP™71 Label Printer provided the roll adapter (M71-ADAPT) is used.
Max. Characters per Line	37
Max. Lines of Text	10
Max. Service Temp. °C	60
Max. Wire/Cable Diameter (mm)	24.30
Min. Wire/Cable Diameter (mm)	10.80
Order Reference	PTL-33-427-YL
Printable Area - Height (mm)	25.40
Printer Compatibility	BMP71; TLS2200; TLSPC Link
Ribbon Series	R4310
Shape	Rectangle
Size - Height (mm)	101.60
Size - Width (mm)	38.10
Additional Information	Self-laminating;Self-Extinguishing;Excellent water & oil resistance;Excellent abrasion and smudge resistance
Total Qty per	100 Label(s) / Roll

