



Product Data Sheet

200 Series - General Purpose Specific Gravity Hydrometers

The specific gravity 60/60°F scale compares the relative density of a given liquid with that of water, at 60°F (15.6°C). The instruments listed are similar to hydrometers included in ISO 650 and in the (now superseded) 1960 issue of British Standard 718.




Image shows
10/502/0

Product Specifications:

- Material:** Soda glass, steel shot ballast, synthetic wax resin
- °SG Ranges:** See table below
- Range:** 0.200 S60/60°F
- Accuracy:** 0.004 S60/60°F
- Divisions:** 0.002 S60/60°F
- Overall Length:** 250mm
- Bulb Diameter:** 18 - 20mm
- Approx Weight:** 42g (including 11g protective plastic tube)

Standard Product Numbers:

Range °SG	To suit Surface Tension	M100 Product No
0.60 to 0.80	Low	10/500/0
0.80 to 1.00		10/501/0
1.00 to 1.20	Medium	10/502/0
1.20 to 1.40		10/503/0
1.40 to 1.60		10/504/0
1.60 to 1.80		10/505/0
1.80 to 2.00		10/506/0

PDS 0505:14:R1

Brannan Thermometers & Instrumentation

Leconfield Industrial Estate • Cleator Moor • Cumbria • CA25 5QE • UK

tel: +44 (0)1946 816600 fax: +44 (0)1946 816625 email: sales@brannan.co.uk web: www.brannan.co.uk

