

Fan XGT®

CF002G

40Vmax • ø 330 mm

Three blowing speeds and a timer function.

This 330 mm XGT® battery or AC powered fan is an excellent companion for the summer heats. Tilts up and down and rotates left to right for convenient redirection of air flow.



Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Max. Air Velocity	4,0 / 2,8 / 2,0 m/s
Air volume	21 / 15 / 10 m³/min
Continuous Use XGT® 40V Max / 4.0 Ah	17 / 10,5 / 5,5 h
Diameter (D)	330 mm
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Tool weight with battery	4,5 - 5,7 kg
Product net weight	3,8 kg
Product Dimensions (L x W x H):	277 x 439 x 602 mm
Angle range horizontal	180 °
Angle range vertical	135 °
Automatic rotational angle (left / right)	45 °

User benefits

- Easily removable fan cover for convenient clean-up
- Can be loaded on optional tripods
- Designed to withstand harsh job site environments
- Three speed settings (High/Medium/Low) and oscillation selector for optimal air velocity and control
- Strong enough to create a comfortable work environment under hot weather conditions
- Battery protection system automatically shuts off power when the battery level is low
- 3-stage automatic timer with 1, 2, and 4 hour power-off selection

Link to product - www.makita.com



Related products

Other

User manual

Parts drawing