

Zarges Fibreglass 3-Part Skymaster



ZARGES FIBREGLASS SKYMASTER™

3-Part fibreglass combination ladder with 10 year guarantee

The Skymaster™ has been a great success for many years, with both the aluminium Industrial and Trade versions becoming a hit with users across the country. Now the Skymaster™ has been manufactured for use around electrical hazards using insulated fibreglass (GRP) stiles.

Available as an 8 rung ladder (3 sections x 8 rungs), the Fibreglass Skymaster™ is ideal for use on railways, in power stations or simply around cabling and electrical hazards.

Fibreglass Skymaster™, the best of Skymaster™, for electrical environments.

- 3 section fibreglass ladder
- Aluminium side locking arm for “A” frame configurations
- Wide stabilising base with anti-slip feet
- Lockable ladder sections for transport or during use
- Anti-splay, nylon straps
- Stile guide anti-friction plastic inserts protect ladder sections from damage
- Tough, replaceable plastic end caps secure the ladder in position
- ‘Angle finder’ helps position ladder in lean-to applications
- Certified to EN131 (150 kg static load rating)

Product code	Number of rungs	Closed length (m)	2-part extended length (m)*	3-part extended length (m)	Weight (kg)
GRP41521 RS: 7990632	3 x 8	2.45	4.10	5.80	27.5