

## 3549-00 UK

### Torque wrench TORCOFLEX UK

1-550 Nm

Code	ETIM
2958007	EC002132
EAN	UNSPSC
4002805935521	27-11-17-15
Country of origin	eCl@ss
Germany	21-04-02-22
Customs tariff number	
82041100	



### Article description

- Adjustable, releasing and sturdy tubular torque wrench with integrated lever ratchet (from 3/4 inch with change disk) and with square drive for industry and the trades
- Classified to DIN EN 6789: 2017 type II class A calibrated to a max. admissible deviation of +/- 3 % and therefore more precise than +/- 4 % required by the standard
- Incl. test certificate according to DIN EN ISO 6789-2:2017
- For controlled clockwise tightening

### Article information

Contents (Qty of pieces)	1	Torque range (min./max.) [N·m]	1 Nm - 5 Nm
Net weight [kg]	0,61 kg	Trigger mechanism	Short path triggering
Total length [mm]	225 mm	Precision +/-	+/- 6 %
Total width [mm]	34 mm	Direction of tightening	Right
Total height [mm]	34 mm	Fixed setting	no
Material	Steel tube construction with high-quality plastic parts	Test certificate	DIN EN ISO 6789-2:2017
Drive connector square (male)	1/4"	Graduation	0,25
Drive connector square (male)	6,3 mm	Head height 1 [mm]	15 mm
Return angle	15°	Width of head 1 [mm]	25,0 mm
Number of teeth	24	Calibration length	152 mm
Drive type/drive	Reversible ratchet	vernier Nm	0,025 Nm
Torque (min.) [N·m]	1 Nm	Distance housing - square drive	12,5 mm
Torque (max.) [N·m]	5 Nm		