



RSHEY20-TV-VA

Plummer block housing unit

Plummer block housing unit RSHEY..-TV-VA,
RIBB plastic

Technical information

Your current product variant

Special material	TV	Plastic housing
Corrosion resistant bearing	VA	Corrosion-resistant VA design
Material	TV	Plastic

Main Dimensions & Performance Data

d	20 mm	Bore diameter
L	72.8 mm	Length
H 2	66 mm	Height
≈m	0.272 kg	Weight

Mounting dimensions

J	50.8 mm	Distance fixing bore
K	M8	Thread fixing bore

Dimensions

H	33.3 mm	Distance shaft axis
A	34.5 mm	Width (base)
S	18.3 mm	Distance raceway
B	31 mm	Width
Q	1/4 - 28 UNF	Connection thread for lubrication



Additional information

GEH-SHE04-TV	Housing
GYE20-KRR-B-FA107-VA	Bearing designation
KASK04-S-G	End cap
KASK04-S-R-NBR	Open protecting cap

Temperature range

T _{min}	-20 °C	Operating temperature min.
T _{max}	80 °C	Operating temperature max.