



Part Number : [1300640496](#)

Product Description : BradPower D-Size (1 3/8"-M35) Double-Ended Cordset, 3 Poles, Male (Straight) to Female (Straight), 10 AWG, Black TPE Cable, Red Overmold, 20.0m (65.62') Length

Series Number : 130064

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Number : CC3030K19M200E

Documents & Resources

Drawings

[1300640496_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead; diphenyl(2,4,6-trimethylbenzoyl)phosphine oxide per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	130064
Description	BradPower D-Size (1 3/8"-M35) Double-Ended Cordset, 3 Poles, Male (Straight) to Female (Straight), 10 AWG, Black TPE Cable, Red Overmold, 20.0m (65.62') Length
IP Rating	IP67
Product Name	BradPower D-Size
Type	Double Ended
UPC	78172550662

Agency

UL	E258922
----	---------

Electrical

Current - Maximum per Contact	32.0A
Voltage - Maximum	600V AC/DC

Physical

Cable Diameter	11.48mm (.452")
Cable Length	20.0m (65.62')
Color - Cable Jacket	Black
Connector End A	BradPower D-Size (1 3/8"-M35)

Connector End B	BradPower D-Size (1 3/8"-M35)
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	None
Material - Cable Jacket	TPE
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Anodized Aluminum
Material - Plating Mating	Gold
Net Weight	20444.000/g
Orientation	Straight to Straight
Poles	3
Temperature Range - Operating	-20° to +90°C
Wire/Cable Type	TC-ER
Wire Size (AWG)	10