

Product data sheet

Specifications



Easy UPS On-Line SRVS 72V RM Battery Pack for 2/3 kVA Extended Runtime Model

SRVS72RLBP-9A

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Number of rack unit	2U
Battery type	Lead-acid battery
Provided equipment	Documentation CD User manual Battery cable Rack mounting brackets

Physical

Colour	Black
Height	8.6 cm
Width	43.8 cm
Depth	63.2 cm
Net weight	42.5 kg
Mounting mode	Rack-mounted with kit
USB compatible	No

Conformance

Product certifications	CE EAC EN/IEC 62040-1
------------------------	-----------------------------

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...3000 m
Ambient air temperature for storage	-15...40 °C
Storage Relative Humidity	Non-condensing 0...95 %
Storage altitude	0...15000 m

Batteries & Runtime

Number of battery blocks per string	6
Device mounting	Rack mount
Number of battery filled slots	0
Number of battery free slots	0
Battery voltage	72 V

Packing Units

Package 1 Weight	53.1 kg
Package 1 Height	24 cm
Package 1 width	60 cm
Package 1 Length	80 cm

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------