

FEATURES

- Impedance of 50 ohms
- Screw-on connection
- Sub-miniature type A connectors
- Variety of cable lengths offered in this range.

RS PRO Black Coaxial Cable, 50 Ω

RS Stock No.: 526-0392



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From the trusted brand RS PRO, comes a range of high quality coaxial cables. Constructed out of industry-standard components, these flexible cables have been designed to carry signals over long distances and are easy to install.

Variety of cable lengths offered in this range. 1m ([5260308](#)), 322mm ([5260392](#)), 520mm ([5260409](#)), 500mm ([5260437](#)), 255mm ([5260487](#)), 1M ([5260314](#)), 255mm ([5260493](#))

General Specifications

Coaxial Type	RG174/U
Connector A	Male SMA
Connector B	Male SMA
Terminated/Unterminated	Terminated
Sheath Colour	Black
Applications	Connecting radio transmitters and receivers with their antennas, Computer network (Internet) connections, Feeding satellite signals through to your TV.

Electrical Specifications

Characteristic Impedance	50 Ω
Voltage Rating	335V

Mechanical Specifications

Length	320mm
Cable Shape	Coaxial

Item	Material
Insulation	PTFE

Operation Environment Specifications

Operating Temperature Range	-40°C to 85°C
Minimum Operating Temperature	-40°C
Maximum Operating Temperature	85°C

Approvals

Compliance/Certifications	EN61340
Standards Met	MIL-STD-348A

