

Solid Blank Panel with Hinge for Server Racks - 6U

Product ID: RKPNLHS6U



You can improve the appearance and airflow of any standard 19-inch server rack, while maintaining easy access, using this 6U blanking panel. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The hinged blanking panel creates a clean and professional look by covering empty space and visible cables. Adding blanking panels to your server racks offers a tidier appearance for a more organized server room.

The blanking panel features a hinged design that enables you to open the panel for fast and easy server access. You can quickly open the panel, make your required adjustments and when you're finished, simply close the panel to restore the professional appearance and order of your server room. The panel is reversible, so you can install it on the left or the right side of your rack.

Plus, the panel includes the screws and nuts you will need to install it in your server rack, to ensure a quick and easy installation.

The blanking panel features a solid design that helps guide airflow down the back of your rack, rather than between occupied spaces. Improved airflow helps ensure your rack-mounted equipment is running at an optimal temperature.

The RKPNLHS6U is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Fill in unused gaps between equipment in server racks and cabinets
- Access your covered rack with an open-and-shut design

- Help guide the airflow along the back of your rack, instead of passing through your equipment

Features

- Create a tidy and professional look by covering unused rack space
- Easily access rack components by opening the hinged panel
- TAA compliant for GSA Schedule purchases
- Versatile installation options with a reversible blank panel that can open from the left or the right side
- 6U, solid rack-panel design
- Mounts to standard 19" 2 or 4-post racks
- Sturdy steel construction
- Rack screws and nuts included

Hardware

Warranty	2 Years
U Height	6U
Industry Standards	EIA RS310-D
Mounting Options	Front Mount (Front Only)

Physical Characteristics

Color	Black
Material	Steel
Product Length	18.3 in [46.5 cm]
Product Width	10.4 in [26.5 cm]
Product Height	0.6 in [15 mm]
Weight of Product	3.2 lb [1.5 kg]

Packaging Information

Package Length	21.1 in [53.5 cm]
Package Width	11.3 in [28.6 cm]



Package Height 1.5 in [38 mm]

Shipping (Package) Weight 3.8 lb [1.7 kg]

What's in the Box

Included in Package 6U Hinged Solid Rack Panel
5/8" #10-32 UNF Screws
#10-32 UNF Cage Nuts
Instruction manual

**Product appearance and specifications are subject to change without notice.*

