

VehiclePro High-Pressure Wash RM 806

Detergent concentrate for high-pressure washing. With a wide area of applications for removing the most stubborn residues left by oil, grease, insects and tree sap. NTA-free.

pH 13
in concentrate



Properties

- Ultra-effective high-pressure detergent for vehicle washes
- Dissolves even the most stubborn residues left by oil, grease, tree sap, mud and insects
- Rapidly effective
- Extremely economical
- Rapidly separates oil/water in the oil separator.
- Tensides biodegradable in accordance with EEC 648/2004
- NTA-free

Usage options

- High-pressure cleaner
- Self-service wash bays

Application areas

Agriculture	Transport and machines
Car dealership and garage	Car/engine wash
Building Industry	Transport and machines
Municipal	Car/engine wash
Haulage contractors, bus operators	Car/engine wash
Self-service wash bays	Cars, commercial vehicles, bicycles

Technical data

Container sizes	Packaging unit	Part number
20 l	1 Piece(s)	6.295-553.0
200 l	1 Piece(s)	6.295-554.0

Application

High-pressure cleaner

- Apply primary mixture with fresh water.
- Set the dosage and temperature on the device
- 1-80°C processing temperature.
- Clean object, working in overlapping sections.
- Allow to soak.
- Reaction time max. 2 min.
- Rinse surface well with clear water.

Self-service washing station

- Insert the product into the system.
- Set the dosage and temperature on the device
- Start washing programme.

Instructions for use

- Do not let the cleaning solution dry out.
- Test on an inconspicuous part for material compatibility.
- Do not apply to unpainted or damaged light metal surfaces.
- Store away from frost.

Warnings and safety recommendations according to EC Directives

- Danger
- H290 May be corrosive to metals
- H314 Causes severe skin burns and eye damage
- P280 Wear protective gloves/protective clothing/eye protection/face protection.
- P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
- P310 Immediately call a POISON CENTER/doctor.
- P303 + P361 + P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water [or shower].
- P405 Store locked up.
- P501a Dispose of contents/container in accordance with local/regional/national/international regulations.

Further information

- Material Safety Data Sheet (MSDS)

Dosage and yield

Contents	Cleaning method	Primary mixture	Dosage	Soiling	Yield
1000 ml	High-pressure cleaner	1+3	0.8 - 2 %	medium	60 Car
1000 ml	Self-service wash bays	1+3	0.8 - 2 %	medium	60 Car