



ENGLISH

## RS Pro Brass Single Check Valve, 1-1/4 in BSP

RS Stock No. 340-3323

Brand RS Pro



# Product Details

## Female/Male Ports

For heating, sanitary and compressed air systems, pumps and autoclaves

Body in hot forged DZR brass

Threading to BS2779

Hostaform inner valve

Spring in 18//8 AISI 302-304 stainless steel

Hydrostatic test pressures 30 bar/435psi (shell), 22 bar/315psi (seat)

Compact design, allows flow in one direction only, indicated by arrow on valve body

Installation in vertical, horizontal or oblique pipelines

Snap-in, spring loaded non- return valve, WRC approved

Low pressure drop, prevents water hammer

Full flow area equal to nominal size

## Non Return Valve-Spring Loaded And Wafer

---

Add product to Compare

---

# Specifications

Not what you're looking for? Select the attributes you require, then click the button below

<input type="checkbox"/> Type	Single
<input type="checkbox"/> Connection	1-1/4 in BSP
<input type="checkbox"/> Body Material	Brass
<input type="checkbox"/> Maximum Working Pressure	16 bar
<input type="checkbox"/> Thread Size	1-1/4in
<input type="checkbox"/> Thread Standard	BSP

---