

Product Specification PDF

Date	Correct as of 11th Sep 2025
Brand	C.K Tools
Product	T3896
Description	Ecotronic Anti-Balistic Slim Side Cutters
Barcode	5013969251272
Commodity code	8203200000
Country of origin	TW



Features & Benefits

- ~ Lightweight, precision side cutters for fine cutting applications. ~ The anti-ballistic function captures and contains off-cuts, preventing unwanted dispersion. ~ Suitable for cutting soft copper wires of up to 1.3mmØ / 16AWG. ~ Slim, tapered head for access in confined spaces. ~ Sharp, precision ground cutting edges with a full flush cut. ~ Special tool steel blade, hardened for long-term cutting performance. ~ Electro-static discharging handles
- dissipative 1x10⁶+ ~ Contoured, dual component handle design for comfortable working. ~ Black oxidised finish for corrosion resistance and reduced glare. ~ Smooth-action return spring for convenience during repetitive work. ~ Joint with durable stainless steel rivet. ~ Technical information: ~ Total length: 139 mm ~ Blade length: 9 mm ~ Cutting angle: 21° ~ Head Height (from joint to tip): 18 mm ~ Head Width (Widest point): 10 mm ~ Steel Thickness: 2,5 mm ~ Cutting Capacity (Copper only) : 1,3 mm / 16 AWG

Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	-	100
Width mm	80	82	-	-
Depth mm	19	20	-	-
Height mm	140	170	-	1.78'
Weight	73	90	-	12
Packaging Information	Card use	Cardboard	-	carton
	Card gms	17	-	1000
	Plastic use	No	-	-
	Plastic gms	No	-	5
	Metal use	No	-	-
	Metal gms	No	-	0
	Timber use	No	-	-
	Timber gms	No	-	No