

FG-470



Quick and secure test on the function of wrist strap as being worn

User-friendly design

- A user-friendly pad secures pass/fail judgement on a wrist strap.
- A banana jack on the front panel makes it easy to plug and unplug a wrist strap.



Model No.	Packing List	
FG-470		• Unit • 006P 9V dry battery(for trial) • Grounding wire • Banana plug • Mounting holder • Wood screw (qty 4) • Instruction manual

Model No.	FG-470
Power supply	006P 9 V dry battery (alkaline cell recommended)
Indication : LOW	$R < 800\text{ k}\Omega$
Indication : PASS	$800\text{ k}\Omega \leq R \leq 9\text{ M}\Omega$
Indication : HIGH	$R > 9\text{ M}\Omega$
Time of continuous use	Approximately 50,000 times (9 V alkaline)
Grounding wire	1 m
Operating environment	Ambient temperature / Humidity range : 0 to 40℃, max. 80% RH (without condensation)
Dimensions	85 (W) × 44 (H) × 90 (D) mm 92 (W) × 48 (H) × 97 (D) mm (with mounting holder)
Weight	120 g 160 g (with mounting holder)

*Weight (excluding battery)

FG-470



リストストラップを装着した状態の良否を瞬時に、確実に判定

使いやすいデザイン

- 押しやすくなったパッドにより、確実性の高いリストストラップの良否判定が可能になりました。
- バナナジャックを前面に配置したため、プラグの抜き差しが容易になりました。



品番	セット内容	
FG470-81		● 本体（お試し用乾電池付き） ● アース線：1m 品番 B5238 ● 固定ホルダー ● 木ねじ：4 コ ● バナナプラグ ● 取扱説明書 ● 登録書(3年保証)
品番	FG470-81	FG470-82
校正	なし	出荷時校正付き
電源	乾電池 9V形（アルカリ乾電池推奨）	
判定：LOW	$R < 800k\Omega$	
判定：PASS	$800k\Omega \leq R \leq 9M\Omega$	
判定：HIGH	$R > 9M\Omega$	
電池寿命	約50,000回	
アース線	1m	
動作環境	使用温度/湿度範囲：0～40℃、80%RH最大（結露なきこと）	
外形寸法	85(W)×44(H)×90(D)mm 92(W)×48(H)×97(D)mm（固定ホルダー取付け時）	
重量	120g 160g（固定ホルダー取付け時）	

※重量は乾電池を除きます。

※出荷時校正付きは「校正証明書・検査成績書・トレーサビリティ体系図」が付属しています。
購入時は書類の宛名を販売店にお伝えください。