

VARTA Indestructible H20 Pro 3AAA with Batt.



Extremely robust (3m drop test, IP67) LED Headlight with two light levels, swileing head, adjustable head strap and impact resistance rating of IK08.



Information

- Extremely robust (3m drop test) headlight with shock-absorbing rubber elements
- Impact resistant lens and reflector
- impact resistance rating IK08 (IEC 62262)
- Rugged construction
- 3m drop test
- Water and dust proof (IP67)
- Bright high performance LED
- 2 light levels: high and low
- Swiveling head for optimum illumination of the surroundings
- Head strap incl. middle strap
- Designed for maximum durability
- Operated with 3AAA batteries (incl)

Article Details

Ordernumber	17732 101 421
Customs Tariff Number	85131000
Country Of Origin	China
Beam Range	(up to) 100.00 m
Runtime	(up to) 23 h
Total light output	(up to) 350 lm
Equipped with	3 x AAA Longlife Power
Product Length / Depth mm	47.00
Product Width mm	68.00
Product Height mm	36.50
Product Weight g	74.50

Logistical Data

	Content (SU)	GTIN / EAN	Facing (mm)	Depth (mm)	Height (mm)	Weight (kg)
VBE (Selling unit)	1	40 08496 987177	100.00	55.00	230.00	0.13
SK2 (Inner carton 2)						
SK1 (Inner carton 1)						
VSK (Master carton)	4	40 08496 987184	250.00	240.00	115.00	0.68
PAL (Pallet)	540	40 08496 987191	800.00	1,200.00	1,185.00	113.20
Layer / Pallet	Master carton / Layer		Master carton / Pallet		Minimum pieces / shipment unit	
9	15		135		4	

All mentioned products and specifications are subject to change. In case of non-availability of any product or item, VARTA Consumer Batteries GmbH & Co. KGaA cannot be held responsible. Some of the products shown may not be available in all countries. The pictures might be different to the original products. Technical changes and errors reserved.
VARTA Consumer Batteries GmbH & Co. KGaA | Alfred-Krupp-Str. 9 | 73479 Ellwangen | Germany
P.O. Box 1363 | 73473 Ellwangen | Germany | Phone (+49) 7961 83 0 | Fax (+49) 7961 83 440

