



Datasheet

Stock No: 210-3678

ENGLISH

RS Pro Magnetic Perforated Steel Sheet, 2mm Hole, 1000mm x 500mm x 0.7mm



Product Details:

Galvanised Steel

- Galvanised perforated sheet
- Can be painted after degreasing
- Selvedged border configuration
- Tolerance on length $\pm 1\%$

Dimensions (mm)					
Pattern	Hole(mm)	Open Area	Pitch I (mm)	Pitch II (mm)	Hole Configuration
1	1.2 ø	42%	1.7	3.2	60°
2	1.5 ø	22%	4	4	45°
3	1.7 ø	45%	2.4	4.1	60°
4	2.0 ø	47%	2.8	4.8	60°
5	3.0 ø	33%	5	8.7	60°
6a	3.0 ø	51%	4	6.9	60°
6	4.8 ø	50%	6.5	11.2	60°
7	6.4 ø	43%	9.2	16	60°
8	8.0 ø	68%	9.2	16	60°
9	6.0 x 6.0	62%	7.6	7.6	Square
10	6.0 x 6.0	52%	9.1	7.6	Staggered
11	4.7 x 4.7	35%	8	8	Square
12	2.4 x 12.7	34%	4.8	15.1	Rect
13	6.0 A/F	79%	6.76	11.63	Hex
14	10.0 x 10.0	59%	13	13	Square
15	1.0 ø	46%	1.4	2.4	60°

Specifications:

Material:	Galvanised Steel
Length:	1000mm
Width:	500mm
Thickness:	0.7mm
Open Area Percentage:	47%
Hole Diameter:	2mm
Hole Layout:	60°
Pattern Number:	4
Magnetic:	Yes