

NEW
ProductWEATHERSAFE
IP66
RATING

WXT204N

Passive
GREY
BUTTON**WXT204N****Weathersafe Vision Twin Gang 13A Switched RCD Socket – Passive**

Weathersafe Extreme Switched RCD Socket gives additional protection against the risk of electric shocks at home and in the garden. Ideal for use with lawnmowers, hedge trimmers etc.

- Weathersafe 'Extreme' impact resistant solid ribbed lid.
- Extra fast action – trips out within 40 milliseconds (BS7288).
- Contacts remain latched when power supply is temporarily lost.
- Impact resistant housing.
- Easy release lid catch.
- Multiple M20 threaded screw-outs.
- Test and reset buttons for safety checks.
- Status flag indicator.
- Spacious design allowing full closure of lid with plug in position.
- Suitable for all 13 amp BS plugs.
- Complies with BS7288 and BS1363.
- IP66 weatherproof rating.

NEW
ProductWEATHERSAFE
IP66
RATING

WXT205N

Active
BLUE
BUTTON**WXT205N****Weathersafe Vision Twin Gang 13A Switched RCD Socket – Active**

Shares all the features of the WXT204N but contacts break when power supply is temporarily lost.

- Weathersafe 'Extreme' impact resistant solid ribbed lid.
- Extra fast action – trips out within 40 milliseconds (BS7288).
- Automatically disconnects both Live and Neutral connections leaving Earth connection intact.
- Trips out when the power supply is temporarily lost. A safety must for machine tool applications.
- Impact resistant housing.
- Easy release lid catch.
- Multiple M20 threaded screw-outs.
- Test and reset buttons for safety checks.
- Status flag indicator.
- Spacious design allowing full closure of lid with plug in position.
- Suitable for all 13 amp BS plugs.
- Complies with BS7288 and BS1363.
- IP66 weatherproof rating.

GREY

BLUE

**Weathersafe
Extreme****Keep Safe Outside**

The tough impact resistant polycarbonate housing means you can expect years of good service from even the toughest environments where the occasional impact is only to be expected.



sales office 020 8452 1112 fax 020 8450 0635

TIMEGUARD

WEATHERSAFE
IP65
RATING

WP401

WP401**Outdoor Multi-Connector Box**

Comes complete with a 4 way, 13 amp socket strip providing the ideal solution for outdoor plug-in power. Ideal for transformer linked garden lighting, fountain pumps, pool filters etc.

- Tough and durable housing.
- 4 gang 13A socket strip included (cable and plug not supplied).
- 1x 20mm cable knock out (mains into socket strip).
- Up to 5x cable seal outlets (to appliances).
- IP65 weatherproof rating.
- Keyhole slot for temporary locating and in-situ alignment.
- Size: 335mm (H) x 220mm (W) x 107mm (D).



See pages 93 & 94 for product specifications.



All these products carry a 3 year guarantee.

WEATHERSAFE
IP66
RATING

WPM02

WPMS1

WPM02**Outdoor Power Connect-2 Mini Box**

This compact 2 way mini-box is an ideal addition to the larger WP401. Using the Timeguard ETU17 timer it is ideal for garden and festive outdoor lighting. It has a tough durable housing and IP66 weatherproof rating.

- Tough and durable housing.
- 2 gang, 13A socket strip included (cable and plug not supplied).
- Multiple appliance cable outlets.
- Spacious design suitable for all 13 amp BS plugs and selective timers.
- Ideal for transformer linked garden lighting and other outdoor appliances.
- IP66 weatherproof rating.
- Keyhole slot for temporary locating and in-situ alignment.
- Size: 230mm (H) x 156mm (W) x 107mm (D).

WPMS1**Ground Spike for use with WPM02**

- Allows free standing garden mounting.

**Weathersafe Outdoor Multi-Connector Boxes**

Timeguard's WP401 and WPM02 come complete with a 13A socket strip providing the ideal solution for outdoor plug-in power. Ideal for transformer linked garden lighting, fountain pumps, pool filters etc.

WP401 shown with ETU17 for timing applications.



TIMEGUARD

email csc@timeguard.com visit our website timeguard.com