









PCB LAYOUT (CONNECTOR REAR VIEW)

- RJ45 CONTACTS
- RJ45 SHELL GROUND CONTACT
- SHIELD BOX LEGS
- CONNECTOR LOCATION PINS



PANEL CUT-OUT



1.2-2.5mm RECOMMEND
PANEL THICKNESS

RJXS8FP5VPE

SERIES PREFIX
CONTACT LAYOUT (RJ45 STYLE)
GENDER
FOUR HOLE RECEPTACLE HOUSING IP65, WITH CAP (BLACK)
TRANSMISSION CLASS (CAT5e)
VERTICAL MOUNT (PCB THRU HOLE)
POTTED
WITH EMI/RFI SHIELD

RECOMMEND MINIMUM MOUNTING PITCH



UNLESS OTHERWISE SPECIFIED TOLERANCE TO BE:		THIS DOCUMENT IS THE PROPERTY OF AMPHENOL AUSTRALIA PTY. LTD. NO PART THEREOF MAY BE REPRODUCED AND USED WITHOUT THE PRIOR WRITTEN CONSENT OF THE OWNER				Amphenol		Amphenol Australia Pty.Ltd, 22 Industry Blvd Carrum Downs, VIC 3201	
LINEAR	ANGULAR	MATERIAL:	DRN:	J.W	DATE: 30/12/2024	TITLE:	PART NO:		REV
X ±10 X.X ±5 X.XX ±1	X° ±1 X°X' ±30' X°XX' ±15'		CKD:	P.M	DATE: 30/12/2024		XLNet, VERT, IP65, POTTED, SHIELDED, W/CAP, PANEL THICKNESS 1.2-2.5	RJXS8FP5VPE	1
BREAK ALL SHARP EDGES AND REMOVE ALL BURRS		SEE COMPONENTS		APP'D:	P.M	DATE: 30/12/2024	DRAWING NO.		SHEET
DO NOT SCALE		FINISH: SEE COMPONENTS		SCALE:	NTS	SIZE: A3	55011419-000-1		2/3
DIMENSIONS IN MILLIMETRES				THIRD ANGLE PROJECTION					