
Features

- Grade 10 connecting link for assembling chain slings
- Available from 6mm to 32mm lifting chains
- Available from 1.4t to 40T Working Load Limit
- Locking spring encapsulated in a protective steel bushing
- Luminous red powder painted finish

RS PRO Connecting Link Range, Grade 10



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Connecting Link Range

The RS PRO Connecting Link is a Grade 10 lifting chain component designed for quick and cost-effective assembly of chain slings. It is suitable for connecting compatible chain, hooks, master links and other lifting components within a correctly rated chain sling assembly.

The locking spring is encapsulated in a protective steel bushing, helping to protect the locking mechanism and provide a secure connection during use. The RS Pro connecting link forms part of a wider Grade 10 component range available for chain sizes from **6mm to 32mm**, with working load limits from **1.4t to 40t**.

Grade 10 components offer a higher lifting capacity than traditional Grade 8 components and are designed for demanding lifting applications. Each component is type tested and fatigue rated to **20,000 cycles at 1.5 times the WLL**, with full traceability through batch marking.

The component is finished in luminous red powder paint and is suitable for use in temperatures from **-40°C to +200°C** without reduction in WLL. It meets **EN 1677-1 +25% WLL** and **AS 3776**, with a safety factor of **4:1**.

It may also be used with Grade 8 chain to **EN 818-2**, provided the complete chain sling is rated as Grade 8 in accordance with **EN 818-4**.

General Specifications

Product Type	Lifting Hooks
Sub Type	Connecting Link
Material	Grade 10 Alloy steel
Working Load Limit	See details below
Weight	See details below
Standards/Approvals	EN1677

Stock No.	Product Name	Working Load Limit	Weight kg
904897	Connecting Link	1.4t	0.08
904898	Connecting Link	2.5t	0.18
904888	Connecting Link	4t	0.34
904890	Connecting Link	6.7t	0.68
904891	Connecting Link	10t	1.22
904892	Connecting Link	16t	2.13
904893	Connecting Link	19t	3
904894	Connecting Link	26.5	5.22
904896	Connecting Link	40	9.55

Approvals

Declarations	REACH DoC and 2.2 Certificate
Standards Met	EN1677

Similar Products

Stock No.	Brand	Product Name	Product Type	Working Load Limit	Weight (kg)
904899	RS PRO	Lifting Hook	Container	16t	4
904900	RS PRO	Lifting Hook	Container	16t	4
904901	RS PRO	Lifting Hook	Container	16t	4
904897	RS PRO	Lifting Hook	Connecting Link	1.4t	0.08
904898	RS PRO	Lifting Hook	Connecting Link	2.5t	0.18
904888	RS PRO	Lifting Hook	Connecting Link	4t	0.34
904890	RS PRO	Lifting Hook	Connecting Link	6.7t	0.68
904891	RS PRO	Lifting Hook	Connecting Link	10t	1.22
904892	RS PRO	Lifting Hook	Connecting Link	16t	2.13
904893	RS PRO	Lifting Hook	Connecting Link	19t	3
904894	RS PRO	Lifting Hook	Connecting Link	26.5	5.22
904896	RS PRO	Lifting Hook	Connecting Link	40	9.55
904910	RS PRO	Lifting Hook	Self-Lock w/ Eye	1.4	0.5
904911	RS PRO	Lifting Hook	Self-Lock w/ Eye	2.5	0.9
904903	RS PRO	Lifting Hook	Self-Lock w/ Eye	4	1.5
904904	RS PRO	Lifting Hook	Self-Lock w/ Eye	6.7	2.7
904905	RS PRO	Lifting Hook	Self-Lock w/ Eye	10	5.7
904906	RS PRO	Lifting Hook	Self-Lock w/ Eye	16	7.9
904907	RS PRO	Lifting Hook	Self-Lock w/ Eye	19	11.2
904908	RS PRO	Lifting Hook	Self-Lock w/ Eye	26.5	20.5
904909	RS PRO	Lifting Hook	Self-Lock w/ Eye	40	40.4
904879	RS PRO	Lifting Hook	Sling Hook	1t	0.7
Stock No.	**Brand**	**Product Name**	**Product Type**	**Working Load Limit**	**Weight (kg)**
904880	RS PRO	Lifting Hook	Sling Hook	2t	1.3

904881	RS PRO	Lifting Hook	Sling Hook	3t	2.3
904882	RS PRO	Lifting Hook	Sling Hook	5t	4.6
904886	RS PRO	Lifting Hook	Sling Hook with Swivel	1.4	0.65
904887	RS PRO	Lifting Hook	Sling Hook with Swivel	2.5	0.95
904883	RS PRO	Lifting Hook	Sling Hook with Swivel	4	1.7
904884	RS PRO	Lifting Hook	Sling Hook with Swivel	6.7	3.1
904885	RS PRO	Lifting Hook	Sling Hook with Swivel	10	5.4
904877	RS PRO	Lifting Hook	Sling Hook with Eye	1.4t	0.27
904878	RS PRO	Lifting Hook	Sling Hook with Eye	2.5t	0.65
904912	RS PRO	Lifting Hook	Sling Hook with Eye	4t	1.22
904913	RS PRO	Lifting Hook	Sling Hook with Eye	6.7t	2.43
904871	RS PRO	Lifting Hook	Sling Hook with Eye	10t	3.81
904872	RS PRO	Lifting Hook	Sling Hook with Eye	16t	6.2
904874	RS PRO	Lifting Hook	Sling Hook with Eye	19t	11.5
904875	RS PRO	Lifting Hook	Sling Hook with Eye	26.5t	12.2
904876	RS PRO	Lifting Hook	Sling Hook with Eye	40t	17.5