

LONG LIFE CUTTING METAL

PRO

- 1 Robust aluminium oxide grains for long-lasting performance
- 2 Resin matrix for strength and resistance to heat
- 3 Strong fibreglass net reinforces the disc



BOSCH

PRO METAL BONDED CUTTING DISC

PRO


- ▶ For cutting metal in general metalworking applications
- ▶ Highly efficient for metalworkers: Long Life
- ▶ Designed for cutting metal
- ▶ With 25.4 mm bore for metal cut-off saws



PRODUCT PROPERTIES						ORDERING INFORMATION						
Specification	Diameter mm	Bore diameter mm	Thickness mm	X-LOCK	oSa	Packaging type	Pack quantity	Minimum order quantity	Barcode 3 165 140...	Part number		
StraightAppropriate for chop saws/stationary pendulum action cuttersMaximum drive power of 3 bhp/2.4 kWMaximum drive power of 3 bhp/2.4 kW												
A 36 R BF	305	25.40	2.8	-	●	U0	1	10	218 641	2 608 600 542		
A 30 T BF	355	25.40	2.8	-	-	U0	1	10	777 230	2 608 601 238		
A 36 R BF	355	25.40	3.0	-	●	U0	1	10	218 658	2 608 600 543		
A 36 R BF	405	25.40	3.4	-	●	U0	1	10	218 665	2 608 600 544		


BOSCH