

MARQUARDT



Product number	1550.1902
Miscellaneous	standard switch without ECO function
Switching function	ON / OFF switch (SPST)
Number of poles	1-pole
connections	Quick-connect terminal, 4.8
Mechanical life endurance	5E4
Rating IEC	7 A 250 V AC 5E4
Contact resistance (new condition)	< 100 (1 A 12 V DC) mOhm
Insulation resistance (new condition)	> 100 (500 V DC) MOhm
Proof tracking	250 PTI
Protection type	Connection IP 40
Ambient temperature	-20 °C ... +85 °C
Ambient temperature	-20 °C ... +55 °C
Flammability	UL 94 V-0
Glow wire test temperature	850 °C
Actuators and additional actuators	PA, black
Housing description	PA, beige
Contact material	Ag
Contact distance	≥ 3 mm
Lighting	230 V
Plug force of the terminals	≤ 80 N
Approval marks	ENEC 15 / cULus
Suitable for appliances of protection class	II
EN 60335 cap. 30 conform "G"	yes

