



ABSU 12 C

2-speed cordless drill/driver

Order number: 7 113 20 61 00 0



Powerful and light cordless drill/driver with fixed drill chuck.

- Powerful and long-life DC motor with overheating and overload protection.
- Robust solid metal drill chuck with chucking force safety device.
- Short design of 180 mm.
- Perfect for use with stepped drill bit, e.g. for drilling initial holes in sheet metals.
- 17 torque levels – force can be easily metered up to 20 Nm for tough screw connections.
- 2-speed solid metal gearbox.
- Bright LED light on housing.
- 2.5 Ah battery capacity for up to 350 screw connections (5 x 40 mm).
- FEIN SafetyCell technology. Protects the battery and tool from overload, overheating and total discharge.
- The battery charge can be read off the battery.
- Includes belt holder and magnetic bit holder.
- One charger for all FEIN Li-ion batteries of all voltage classes.



ABSU 12 C

2-speed cordless drill/driver

Order number:: 7 113 20 61 00 0

Technical data

| | |
|----------------------------|-----------------|
| Battery voltage | 12 V |
| Battery capacity | 2,5 Ah |
| Motor | 2-pole DC |
| Gearbox | 2-speed |
| Speed, no load | 400 / 1 300 rpm |
| Max. torque (hard/soft) | 20 / 14 Nm |
| Torque levels | 17 + 1 |
| Drill chuck clamping width | 1 - 10 mm |
| Fastening | 6 x 200 mm |
| Capacity in steel Ø | 10 mm |
| Capacity in wood Ø | 30 mm |
| Weight with battery | 1,2 kg |
| Cordless | X |

Included in price::

| |
|--------------------------|
| 1 cordless drill/driver |
| 2 battery packs (Li-Ion) |
| 1 belt clip |
| 1 bit holder |
| 1 rapid charger ALG 50 |
| 1 plastic carrying case |