

FEATURES

- Constant wattage per meter, parallel circuit heating tape
- Cut to length
- Flexible can be wrapped around pipes
- Various lengths available - 20m, 50m or 100m
- Voltage ratings either 110V or 240V

RS PRO Trace Heating Termination Kit, -60 \rightarrow +200 °C

RS Stock No.: 256-109



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

RS PRO range of parallel circuit heating tape, with a constant wattage output for process temperature maintenance applications. This tape is flexible enough to allow it to be spiralled around a suitable pipe or vessel. The heating tape consists of several short heating zones each connected across a pair of continuous bus-wire conductors.

Trace heating options include:

703-3108 - 15W/m, 110 V, 20m cable

703-3101 - 15W/m,110 V, 50m cable

703-3105 - 15W/m, 110 V, 100m cable

256-244 - 15W/m, 240 V, 20m cable

665-7419 - 15W/m, 240 V, 50m cable

665-7413 - 15W/m, 240 V, 100m cable

256-109 - Trace Heating Termination Kit

General Specifications

	Туре	Termination Kit
--	------	-----------------

Kit contains:

Quantity	Item Name
3	End seal moulds
3	End seal moulds
1	Tube of silicon adhesive
3	Warning labels
3	O Ring Crimp

Electrical Specifications

Maximum Voltage	110V or 240V
-----------------	--------------



Operation Environment Specifications

Operating Temperature Range	-60°C to 200°C
Minimum Operating Temperature	-60°C
Maximum Operating Temperature	200°C

Approvals

Compliance/Certifications	RoHS
---------------------------	------

