

Encodercbl. Dunker LPEn1 HD 1,5m



Image is for illustration purposes only. Please refer to product description.

Part number	61 88 720 0006 0150
Siemens part number	HRT:6172060150
Specification	Encodercbl. Dunker LPEn1 HD 1,5m
HARTING eCatalogue	https://harting.com/618872000060150

Identification

Specification	Pre-assembled on both sides
Connector 1	LP 14 poles
Connector 2	M16 Female 12 poles
Type of cable	Copper cable (round)
Description of the cable	Oil resistant Halogen-free Silicone-free
Features	Highly flexible Drag chain compatible

Version

Cable length	1.5 m
Core structure	6x 2x 0.25 mm ²
Field of application	for encoder connection

Termination data

Nominal voltage	60 V DC
-----------------	---------

Technical characteristics

Limiting temperature	-20 ... +80 °C unmoved -20 ... +80 °C moved
----------------------	--



Pushing Performance
Since 1945

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Grey

Specifications and approvals

Specifications	IEC 60332-1 Flame retardancy
----------------	------------------------------

Commercial data

Packaging size	1
Country of origin	Germany
European customs tariff number	85444290
GTIN	5713140275355
eCl@ss	27060307 Bus cable
ETIM	EC002599
UNSPSC 24.0	26121600