

# RAD-ISM-2400-ANT-OMNI-2-1

Order No.: 2867461



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2867461>

Omni-directional antenna, IP65 degree of protection, linear vertical, 2 dBi gain, cable length 1.5 m, MCX (male) connection, impedance 50  $\Omega$ , apex angle h/v 360°/75°

Commercial data	
EAN	4017918952761
Pack	1 Pcs.
Customs tariff	85177011
Weight/Piece	0.0863 KG
Catalog page information	Page 467 (IF-2007)

**Product notes**

WEEE/RoHS-compliant since:  
01/18/2007



<http://www.download.phoenixcontact.com>  
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data	
<b>General data</b>	
Horizontal beamwidth	360 °
Vertical beamwidth	75 °
Impedance	50 $\Omega$
Gain	2 dBi

Type of connection	MCX (male) with cable (1.5 m)
Degree of protection	IP65
Ambient temperature (operation)	-20 °C ... 65 °C
Ambient temperature (storage/transport)	-30 °C ... 75 °C
Width	7.8 mm
Height	82.5 mm

**Address**

PHOENIX CONTACT Ltd  
Halesfield 13  
Telford Shropshire TF7 4PG,GB  
Phone 01952 681 700  
Fax 01952 681 799  
<http://www.phoenixcontact.co.uk>



© 2008 Phoenix Contact  
Technical modifications reserved;