

# GCM 18V-216 Professional



Specification	
Voltage	18
Saw blade diameter	216
Cutting capacity vertical 0° / 45°	70 / 45
Cutting capacity horizontal 0° / 45°	270 / 190
Mitre angle range	47 L / 47 R
Bevel angle range	45 L / 0 R
Weight w/o battery / with 8.0 Ah	14,7 / 15,7
Tool dimensions	520 x 770 x 630
No-load speed [1/min]	4600
Part number	0601B41000

**Cordless miter saw now  
better than corded miter saw**

**BITURBO**  
BRUSHLESS

Key Product Features	Consumer Benefit
High performance	Equal to a corded 1.600W saw due to new BITURBO brushless motor and ProCORE18V batteries.
Best in class cutting depth	Cutting depth of 70mm best in 216mm saw-blade class due to optimized tool design
Mobility at its best	Light weight and great ergonomics with handle allowing one hand carrying
Tool-less blade change	SDS lock making saw blade change's fast and uncomplicated
Easy and smooth sliding function	Perfectly centered rails offer smooth and effortless sliding
3 year tool warranty*	100% consumer confidence



**You Tube** [youtube.com/BoschProfessionalUK](https://youtube.com/BoschProfessionalUK)

**f** [facebook.com/BoschProfessionalPowerToolsUK](https://facebook.com/BoschProfessionalPowerToolsUK)



**BOSCH**  
Invented for life

\* Please register your tool, lithium-ion battery or charger online within four weeks of purchase to become eligible for the warranty services Bosch provide