




[All Low & Medium Power Header \(64\)](#)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # 1-967242-1
JPT GEH KPL 16P



TE Part # 963216-1
DICHTUNG

Customers Also Bought




TE Part #1676445-2
RN 0805 82R5 0.1% 10PPM 1KRL




TE Part #1879501-5
CRGH2512 5% 1R5 2W



TE Part #5-1879234-2
SMF5 68K 5%



TE Part #3-2176316-9
MELF SMA_A 120R 1% 50PPM 0207 1W




TE Part #CAT-C339-T547B
Metal Chip Resistor: Current Sense




TE Part #1-776275-1
8POS,PIN DIA 1.3,HDR ASSY,180DEG, COD 1



TE Part #1-188275-0
MICRO-MATCH SMD FTE



TE Part #776349-3
PIN, SF, SIZE 16, 18-20 AWG, NI/SN



TE Part #1544550-2
MODULE AUTOFUSE

Documents

Product Drawings
3MM TAB HEADER ASSY 180

English

CAD Files
Customer View Model
ENG_CVM_CVM_1-1452721-1_B.2d_dxf.zip

English



3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-1452721-1_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1452721-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

JPT SERIES CONNECTORS

English

Product Specification

English