

Features

- The LED torch features a high visibility yellow body
- High Impact LENS & Non-Slip Handle
- Equipped with a safety lock
- ATEX certified which is protection against explosive atmospheres

RS PRO ATEX LED Torches Yellow, 180 lm, 172mm

RS Stock No.: 0145616



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

RS PRO ATEX intrinsically safe LED torch

From RS PRO, comes a high quality and great value ATEX intrinsically safe LED torch. Manufactured with a tough and durable casing and fitted with a CREE LED, this portable, handheld flashlight is an essential solution for use in hazardous locations

Features and benefits:

- High Impact LENS & Non-Slip Handle
- This torch has high and low operating modes that allow users to operate for high brightness or long-duration lighting
- The LED torch features a high visibility yellow body
- Equipped with a safety lock
- Drop resistance of 1 metre
- ATEX certified which is protection against explosive atmospheres
- Beam distance of 117m on the high mode and 83m on the low mode
- Powered by 4 AA alkaline batteries

General Specifications

Torch Style	Straight
Rechargeable	No
Lamp Type	LED
Luminosity	180 lm (high)/ 70lm (low)
Batteries	4 x AA
Case Material	Anti static plastic
Hazardous Area Certification	ATEX
Hazardous Area	Yes
Zone	Zone 0
Range	117M
Beam Type	Spot
Length	172mm
Colour	Yellow
Weight with Batteries	140g
Switching Modes	High/Low/Flash/Off
Light Colour	White

Modes Specifications

Parameters	High Mode	Low Mode / Strobe
Light Output	180lm	70lm
Run Time	11 hours	36 hours
Beam Distance	117m	83m
Switching Modes	Hight/Low/Flash/Off	
Light Colour	White	
Light Colour	White	
Anti-Corrosive	Yes	
Drop Resistance	1m	

Electrical Specifications

Rechargeable	No
Batteries	4 x AA alkaline battery, Ni-MH battery
Battery Indicator	No
Switch Type	Push switch operated by magnetism






Mechanical Specifications

Length	172mm
Width	47 mm
Depth	47 mm
Weight	140g

Protection Category

IP Rating	IP68
-----------	------

Approvals

Compliance/Certifications	CE / UL / ATEX / IECE /
Standards Met	 Class I Div 1&2 Grp ABCD Class II Div 1&2 Grp EFG Class III Temp Code: T4  UL 22 ATEX 2935X UL23UKEX2857X II 1G Ex ia IIC T4 Ga I M1 Ex ia I Ma  IECEX UL 22.0113X Ex ia IIC T4 Ga Ex ia I Ma  0518  2813
Hazardous Area Certification	ATEX; IECEX
Declarations	

Similar Products

Stock No.	Brand	Product Name	Luminosity	Batteries	Colour
0145616	RS PRO	ATEX Torch	180 lm (high)/ 70lm (low)	4 x AA	Yellow
0145619	RS PRO	ATEX Head Torch	200lm (high)/ 100lm (low)	3 x AAA	Yellow
0145618	RS PRO	ATEX Torch	133lm (high)/ 32lm (low)	4 x AA	Yellow