

Nylon steel rod



Description:

- Ideal for long ducts.
- High traction power.
- Breakage load: 200 kN.
- Rod length: 50 m.
- Diameter 6 mm.
- Supplied with: - 1 flexible guiding head. - 1 slide wheel with swage. - 1 snap hook.

	Weight [g]
629896	200.0