



Lighting **excellence**



@4liteuk



@4liteuk



@4lite



@4liteuk

# T8 LED Tube CCT

T8 LED Tube CCT 600mm

Code: 4L3/3000

**Application** Industrial

## Product Features

- Energy-efficient T8 LED glass tube
- Adjustable wattage, allowing selection between high or low output
- Easy to install and the perfect replacement for traditional fluorescent T8 tubes
- Instant light output
- Suitable for residential and commercial applications
- 3 CCT selectable between 3000K, 4000K, and 5700K
- High efficacy up to 140 lm/w
- 5 year warranty

### Technical Information

|                                         |                        |
|-----------------------------------------|------------------------|
| <b>Wattage</b>                          | 5W / 9W                |
| <b>Lumens Delivered</b>                 | 700lm / 1300lm (4000K) |
| <b>Lm/W</b>                             | 140lm/w / 150lm/w      |
| <b>Beam Angle</b>                       | 360                    |
| <b>CRI</b>                              | 80                     |
| <b>CCT</b>                              | 3000/4000K/6500        |
| <b>Input</b>                            | 220-240V               |
| <b>Operating Temp</b>                   | -20°C to 45°C          |
| <b>SDCM</b>                             | 6                      |
| <b>Product Weight without Packaging</b> | 0.107 kg               |

### Technical Information

|                            |                 |
|----------------------------|-----------------|
| <b>Light Source</b>        | T8              |
| <b>IP Rating</b>           | IP20            |
| <b>Class Protection</b>    | 2               |
| <b>Internal / External</b> | Internal        |
| <b>Lumen Depreciation</b>  | L70 B50 25,000h |
| <b>Warranty (Years)</b>    | 5               |
| <b>CE Mark</b>             | Yes             |

