

Product data sheet

9032 M-1

EAN-No. 4000896227099



Length: 115 mm



Application:

Lightweight, handy device for grinding, polishing, burnishing and deburring

- For working in areas with difficult access
- **Straight design**
- Exhaust air is guided through the handle
- Air connection inlet: inside thread (IG) 12.91 mm (1/4")
- Coupler plug: Nominal size 7.2 (included)
- Hose diameter (recommended): 10 mm
- Working pressure (bar): 6.3
- Sound power level: 93.4 db(A) Lp W
- Vibration acceleration: 1.80 m/s²
- Collet chuck: 6 mm
- Power in watts: 224 Watt
- Cold insulated handle
- Dimensions: 115 mm
- Net weight: 0.33 kg
- Sound pressure level: 82.4 dB(A) Lp A
- Revolutions per minute: 25000
- Air requirement: 84 l/min (1.4 l/sec)

"Mini" pneumatic tools range

- Innovative 5-slat concept for even more power than conventional drives
- High reliability and continuous operation

Handle

Cold insulated handle