

Datasheet

RS PRO Stainless Steel, Vertical Mount Flow Switch

RS Stock No: **312-7164**



- Internal fitting via 1/8" BSP
- Stainless steel 316
- Miniature Design
- Temperature up to 120°C
- User configurable N/O (make on rise) or N/C (make on fall)

Technical Specifications

Mounting Style:	Internal
Mounting Thread:	1/8" BSP
Float & Stem material	316 grade SS
Max. Temperature	120°C
Max. Pressure	10 bar
Float SG	0.7

Cable Length	30cm
Cable Size	17/0.10 – AWG22
Cable conductor	Tinned copper
Cable sheath	XLPE
Cable temperature	125°C
Min. fluid SG	0.8

The 312-7164 is a compact vertical internally mounted device. Mounting is in the top or bottom of the tank from the inside, so requires access to the inside of the tank. These are manufactured in 316 grade Stainless steel. The switch action may be reversed by removing the float, inverting and then refitting it to the stem.

