

1839W/K2

Kit of wireless lamps 1838SW and 1836AW, with charging base 1839BRW

Kit contents:

- wireless rechargeable, articulated LED inspection lamp 1838SW
- wireless rechargeable LED headlamp 1836AW
- wireless charging base 1839BRW, compatible with the lamps of the kit

FUNCTIONALITY

The kit comprises products performing different functions. What is more, wireless technology makes it possible to do away with cables, which results in a more convenient and tidier charging base.

WIRELESS TECHNOLOGY

Wireless technology means one of the latest innovations for work lighting and allows one's instruments to be easily charged.


Features of articulated inspection lamp 1838SW:

- Dual light emission:
front: LED COB, 3 light intensities: 250 - 500 - 1000 lumens
spot (head): LED SMD, 200 lumens
- Rechargeable 3.6V 3.350mAh Li-ion battery
- 2 charging modes:
wireless base 1839BRW
power supply with USB-C port
- Charging time:
6.5 h with wireless charging base
4.5 h with power supply
- Life battery:
front: 3-5 h
spot (head): 7 h
- 3-LED battery level indicator
- Base can be rotated 180°
- Nonslip rubber body
- Double swinging hook
- Magnets on base and back
- IP65
- IK07

Features of headlamp 1836AW:

- Dual light emission
Main: 3 light intensities LED COB 30 - 200 - 400 lumens



		art.
	018390820	1839W/K2

- n. **1838SW:**
n. **1836AW:**
n. **1839BRW:**