

## Datasheet

# RS Pro 1 (Inlet), 1 (Outlet) port Actuated Ball Valve, 230 V ac

RS Stock No: **910-8526**



## Product Details

RS Pro port actuated ball valve has a supply voltage of 230 V ac with one inlet and one outlet valve of size s.31 mini. This valve has a strong construction and can operate in vacuum line. It is compatible with most industrial fluids.

## Features and Benefits

- Brass according to EN 12165 and EN 12164 specifications
- Chrome plated ball
- Dual sealing system for easy installation
- Blowout-proof brass stem
- 100% seal test guaranteed in accordance to EN12266-1 rate A in either direction
- Shell rating: 40 bar non-shock cold working pressure
- -20 to 120°C temperature range
- Seat rating: delta P max permissible 16 bar
- EN 10226-1, ISO 228 parallel F/F threads
- Silicone free lubricant



**Specifications:**

Maximum Closing Time	25 s
Maximum Opening Time	20 s
Number of Ports Supported	1 (Inlet), 1 (Outlet)
Power Rating	10 W
Supply Voltage	230 V ac
Electrical Connection	3 Wire
Operating Temperature Range	-20 to +80°C