

accessory LED lamp 025, DC connecting cable, AWG16, with socket, UL



Model		
product brand name		SIVACON
product designation		DC socket with cable 2 m
design of the product		AWG 16 with socket
type of light source		LED
Protection class		
protection class IP		IP20
Product details		
product component		
● ON/OFF switch		
● light sensor		
● socket outlet		
product feature magnetic		No
Connections		
type of electrical connection for through-wiring		Plug-in connection
Mechanical Design		
fastening method		miscellaneous
material		plastic
Approvals Certificates		
General Product Ap- proval	other	Environment



[Confirmation](#)

[Environmental Conformations](#)

Further information		
Information on the packaging		
https://support.industry.siemens.com/cs/ww/en/view/109813875		
Information- and Downloadcenter (Catalogs, Brochures,...)		
http://www.siemens.com/lowvoltage/catalogs		
Industry Mall (Online ordering system)		
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR2210-4B		
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)		
https://support.industry.siemens.com/cs/ww/en/ps/8MR2210-4B		
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)		
http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR2210-4B		
CAx-Online-Generator		
http://www.siemens.com/cax		
Tender specifications		
http://www.siemens.com/specifications		

last modified:

4/15/2025 

