

Angle Drill XGT®

DA001G

40Vmax • 136 Nm • 0 – 1 500 min⁻¹

Powerful XGT® Angle Drill.

DA001G is ergonomically designed and lightweight to reduce operator fatigue.



Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
No load speed	0 - 1500 / 0 - 400 min ⁻¹
Max. Torque (2. Gear / 1. Gear)	55 / 136 Nm
Max. Drilling Diameter in Wood	159 mm
Max. Drilling Diameter in Steel	13 mm
Drilling Capacity Wood (Auger Bit)	50 mm
Drilling Capacity Wood (Self-feed bit)	65 - 118 mm
Driving Shank	20UNF / 1/2 "
Drill Chuck Capacity	2 - 13 mm
Vibration Level, Drilling into metal	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Drilling into metal	1,5 m/s ²
Sound Power Level (L _{WA})	95 dB(A)

User benefits

- Lightweight for reduced operator fatigue
- Fall prevention holder also usable as skyhook
- Powerful drilling even large diameter holes
- Twin LED lights with pre-glow and afterglow functions for better illumination and more accurate work
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitaauk.com



Related products

■ Optional AC

821847-7

Plastic Carrying Case



■ Other

User manual

Parts drawing