

Datasheet

RS Pro 1 Channel Digital DIN Rail Time Switch Measures Hours, 12 V dc

RS Stock No: **896-6891**



Product Details

RS Pro time switch with 1 channel, is measured in hours. This digital switch has a voltage rating of 12 V dc. It is available as daily/weekly/pulse switching for precise timing. The switch has a digital LCD display for easy reading of the time and is suitable for DIN rail mounting.

Features and Benefits

- Daily/weekly/pulse switching (depending on model)
- 3 lines text LCD display
- DIN rail mounting
- 25 on/off programs
- LED indication of relay status
- 12/24 hours display format
- 6 years battery reserve
- Simple reset and manual override
- 110-240 V ac supply voltage
- Settable DST and keypad lock feature



ENGLISH

Specifications:

Units Measured	Hours
Battery Life	6 yr
Depth	65 mm
Height	90 mm
Number of Channels	1
Contact Configuration	CO
Segment Length	1 min
Supply Voltage	110 to 240 V dc
Type	Digital
IP Rating	IP20, IP40
Number of Operating Modes	5
Power Consumption	6 VA