

# STANLEY

## STANLEY FATMAX® 5 in 1 Hacksaw

0-20-108



### Features:

- Standard position is a 90 degree hacksaw with large throat depth
- Blade can be quickly positioned to a 45° angle for making flush cuts
- When working in tight spaces, the front section of the frame can be removed like a jabsaw
- Blade can be attached to the front of the hacksaw frame for inside cuts
- Blade storage inside frame so metal or wood cutting blades
- Fully adjustable tension holds blade up to 100kg

### Description:

The STANLEY FATMAX® 5 In 1 Hacksaw is a multipurpose saw that has been designed for cutting a range of materials. The lightweight adjustable frame offers 100 kg blade tension that can be used both at 90° and 45°. The front section of the saw can be removed when working within tight spaces.

Specifications	
Length	430 mm
Teeth	24 TPI
Handle Material	Moulded
Blade material	Bi-material
Application	Metal