

## Datasheet

# 1/2 Inch Drive Reversible Ratchet Handle

RS Stock number [253-116](#)



### Features

#### Material:

Shaft: Drop forged chrome vanadium steel

Driver with gear: Chrome molybdenum steel

Direction Pawls: Powder die casting chrome molybdenum steel

Grips: Nylon

#### Finish

Shaft/Ratchet Handle: Satin chrome plated.

Driver portion: Chemical blackened finish

Grip: Black injection

#### Hardness

Heat treated to HRC- 38~54 (driver portion & shaft)



ENGLISH

### Contents

1 pc - 1/2" Drive quick release reversible ratchet handle with black nylon injection grip (24 teeth pawl type)

Overall length: 275 depth, 45.0 width 47.0, net weight - 725 grams

### Remarks

1. Driver portion meet din-3120 standard overall length, width of ratchet handle and torque load test meet

D-3122 standard.

2. Torque test load - ratchet handle (512nt-m)